

B5**X**900

Compact Walk-Through Boot Scrubber Unit w/ Dual Sole Brushes

The BSX900 is a wet, compact walk-through, sole-only, dual boot scrubber. The user activates the system by stepping onto the platform. Diluted cleaning solution is sprayed onto rotating brushes and transferred onto the boots from a stainless steel venturi dilution valve and metering tip to provide the desired PPM. The BSX900 uses two rotating horizontal sole brushes, has a small footprint, and is ideal for tight spaces and medium traffic applications.



- Compact design for 1 user at a time (15-25 users per minute)
- Solid member stainless steel construction with hinged access grate
- Two removable anti-slip steps
- Bi-directional entry / exit with central emergency stop
- Wash-down rate stainless electrical enclosure, motors, and hardware
- Spray nozzles directed down to prevent over-spray, coating brush prior to boot contact
- Open grate design ensures optimal debris management
- Proximity sensor and spring loaded grate for unit activation with adjustable timer
- Self-draining tub with 2.5" tri-clamp fitting and four adjustable dairy approved feet
- Solenoid activated brush spray system and venturi injector with 1.5 gpm flow rate
- Optional side shields available for additional splash or overspray prevention

Connection Requirements

- Electrical Options:
 - · 115VAC, single phase, 60Hz, 19.1A
 - · 230VAC, single phase, 60Hz, 13.7A
 - · 480VAC, triple phase, 60Hz, 3.9A
- 3/8" Nptf cold water connection, 50psi recommended
- 2½" Tri-clamp drain connection

Throughput • Plants with lower number of employees • 1 user at a time • 15-25 users per minute • Plants with limited/medium open space • Areas with access to water lines • Areas with accessible floor drains Dimensions Height 63" x Width 45" x Length 54" Weight 425 LB

BSX900-DAF-115V Boot Scrubber w/ Dairy Approved Feet - 115VAC, single phase BSX900-DAF-230V Boot Scrubber w/ Dairy Approved Feet - 230VAC, single phase BSX900-DAF-480V Boot Scrubber w/ Dairy Approved Feet - 480VAC, triple phase







Use Alpet® No-Rinse Quat Sanitizer with the BSX900 to aid in the cleaning of footwear prior to sanitization.

